
TOP WAVELENGTH



- 2330 & 2334 nm
- 3240 & 3270 nm
- 3345 & 3375 nm
- 4524 & 4534 nm
- 5184 & 5263 nm



TOP Wavelengths DFB: 1560/1570/1580/1590 nm



Schematic DFB

with spectrum

λ

nanoplus Distributed Feedback Lasers **(DFB)** are specifically designed for high-precision gas detection using tunable diode laser absorption spectroscopy **(TDLAS)**. Our devices operate **reliably** in more than 30,000 installations worldwide. For more than 20 years nanoplus has set the standard for DFB laser technology and is the only manufacturer routinely providing DFB lasers at **any wavelength**.

Key features:

- MONOMODE
- CONTINUOUS WAVE
- ROOM TEMPERATURE
- MODE HOP FREE TUNING



Overgrowth-free DFB device proces-

A **narrow linewidth below 3 MHz** guarantees ultra-precise scanning of the absorption line feature. The **high output power** of **several mW** yields a stronger signal and increases your measurement precision.

Fast and wide wavelength tuning is required for in situ systems. Most customers use a scan rate of 10 kHz and benefit from our very large tuning coefficient.

"Do not change your ideas, let us deliver a laser that fits your application."

Any **custom wavelength** is possible: You tell us what you need and we deliver it. With our

Our excellent spectral purity is characterized

signal to noise ratio against crossinterference.

patented DFB technology we design any wavelength **between 760 nm and 14 µm.**

by a large side mode suppression ratio (SMSR) of > 35 dB, giving your system a low

We offer **various packaging options**, e.g. several free space housings including TEC and NTC, fiber coupling, **collimation** and **custom designs**. What do you require?

If you require **custom specifications**, please contact us. Nearly 80 % of our devices are more or less customer-specific. As nanoplus is a **fully vertically integrated company**, we control the entire process chain from design to packaging. Both nanoplus production facilities are based in **Germany**. To guarantee consistent product quality we apply a strict and **ISO certified quality management system** at all levels.

Our sales and R&D teams have long-standing experience in developing lasers. They will advise you in your design and realization phase as well as after-sales: We make market leaders! TO5, TO56 and fiber coupled butterfly package


Superior Specifications: 1560/1570/1580/1590 nm


nanop

This data sheet reports performance data of a **sample nanoplus DFB laser at 1570 nm with enhanced specifications.** They are equally valid for 1560 nm, 1580 nm and 1590 nm.

Standard specifications are available at: http://nanoplus-usa.com/products/dfb-laser.

These lasers are particularly suitable for hydrogen sulfide (H,S) detection.





Typical room temperature cw spectrum of a nanoplus DFB laser at 1570 nm

Typical mode hop free tuning of a nanoplus DFB laser at 1570 nm by current and temperature

electro-optical characteristics	symbol	unit	min.	typ	max.
operating wavelength (at $T_{_{\mathrm{op}}}, I_{_{\mathrm{op}}})$	$\lambda_{_{op}}$	nm		1570	
optical output power (at λ_{op})	P _{op}	mW		8	
operating current	l _{op}	mA		70	
operating voltage	V_{op}	V		2	
threshold current	I _{th}	mA	10	15	25
side mode suppression ratio	SMSR	dB		> 35	
current tuning coefficient	C,	nm / mA	0.008	0.012	0.020
temperature tuning coefficient	C _T	nm / K	0.08	0.11	0.13
operating chip temperature	T _{op}	°C	+20	+30	+45
operating case temperature*	T _c	°C	-20	+25	+55
storage temperature*	Τ _s	°C	-40	+20	+80

laser packaging options

TO5 with TEC and NTC, black cap, AR coated window

TO56 without TEC or NTC, sealed, window

c-mount without TEC or NTC

butterfly package with TEC and NTC, SM or PM fiber, FC/APC connector

chip on carrier without TEC, with NTC

Technical drawings & accessories are available at: https://www.nanoplus-usa.com/products/packaging

Please contact <u>victor.perez@nanoplus.com</u> for customized specifications, quotes and further questions. Visit the <u>nanoplus website</u> for technical notes, application samples or literature referrals.

nanoplus America Inc., nanoplus-usa.com, phone: +1-720-453-2454, email: victor.perez@nanoplus.com ©copyright nanoplus America Inc. 2021, all rights reserved. Technical data is subject to change without notice. * non-condensing