TOP WAVELENGTH

760.8 nm

1278.8 nm

1392.0 nm

1512.2 nm

1560 - 1590 nm

1651 & 1654 nm

1742.0 nm

1854 & 1877 nm

2004.0 nm

2330 & 2334 nm

3240 & 3270 nm

3345 & 3375 nm

4524 & 4534 nm

5184 & 5263 nm


TOP Wavelengths

DFB: 5184 nm & 5263 nm



Key features:

- MONOMODE
- CONTINUOUS WAVE
- ROOM TEMPERATURE
- MODE HOP FREE TUNING





Any **custom wavelength** is possible: You tell us what you need and we deliver it. With our patented DFB technology we design any wavelength **between 760 nm and 14 µm.**

Our excellent **spectral purity** is characterized by a large side mode suppression ratio **(SMSR)** of **> 35 dB**, giving your system a low signal to noise ratio against crossinterference.

Overgrowth-free DFB device proces-

A **narrow linewidth below 3 MHz** guarantees ultra-precise scanning of the absorption line feature. The **high output power** of **several mW** yields a stronger signal and increases your measurement precision.

Fast and wide wavelength tuning is required for in situ systems. Most customers use a scan rate of 10 kHz and benefit from our very large tuning coefficient.

"Do not change your ideas, let us deliver a laser that fits your application."




If you require custom specifications, please contact us. Nearly 80 % of our devices are more or less customer-specific. As nanoplus is a fully vertically integrated company, we control the entire process chain from design to packaging. Both nanoplus production facilities are based in Germany. To guarantee consistent product quality we apply a strict and ISO certified quality management system at all levels.

Our sales and R&D teams have long-standing experience in developing lasers. They will advise you in your design and realization phase as well as after-sales: **We make market leaders!**











Superior Specifications: 5184 nm & 5263 nm





This data sheet reports performance data of a **sample nanoplus DFB laser at 5263 nm with enhanced specifications.**They are equally valid for 5184 nm. Standard specifications are available at: https://nanoplus-usa.com/products/dfb-laser/.
These lasers are particularly suitable for nitrogen oxide (NO_v) detection.





Typical room temperature cw spectrum of a nanoplus DFB laser at 5263 nm

Typical mode hop free tuning of a nanoplus DFB laser at 5263 nm by current and temperature

electro-optical characteristics	symbol	unit	min.	typ	max.
operating wavelength (at $T_{op'}$ I_{op})	$\lambda_{\sf op}$	nm		5263	
optical output power (at λ_{op})	P_{op}	mW		6	
operating current	l _{op}	mA			120
operating voltage	V_{op}	V		5	
threshold current	I _{th}	mA	25	35	55
side mode suppression ratio	SMSR	dB		> 35	
current tuning coefficient	C	nm / mA		0.14	
temperature tuning coefficient	C_{T}	nm / K		0.48	
operating chip temperature	T_{op}	°C	+15	+20	+40
operating case temperature*	T_{c}	°C	-20	+25	+55
storage temperature*	T_s	°C	-30	+20	+70

* non-condensing

laser packaging options

TO66 with TEC and NTC, black cap, AR coated window

Other packaging options may be discussed on request.

Technical drawings & accessories are available at: https://nanoplus-usa.com/products/packaging/

Please contact <u>victor.perez@nanoplus.com</u> for customized specifications, quotes and further questions. Visit the <u>nanoplus website</u> for technical notes, application samples or literature referrals.