Distributed Feedback Lasers 1300 nm - 1650 nm



WAVELENGTH

760-830 nm

830-920 nm

920-1100 nm

1100–1300 nm

1300-1650 nm

1650–1850 nm

1850–2200 nm

2200-2600 nm

2600-2900 nm

2800-4000 nm

4000-4600 nm

4600-5300 nm

5300-5800 nm


5800–6500 nm

6000-14000 nm

nanoplus Distributed Feedback Lasers (DFB) are specifically designed for high-precision gas detection using tunable diode laser absorption spectroscopy (TDLAS). Our devices operate reliably in more than 50,000 installations worldwide. For 25 years nanoplus has set the standard for DFB laser technology and is the only manufacturer routinely providing DFB lasers at any wavelength.

Key features:

- MONOMODE
- CONTINUOUS WAVE
- ROOM TEMPERATURE
- MODE HOP FREE TUNING



Overgrowth-free DFB device processing A narrow linewidth below 3 MHz guarantees ultra-precise scanning of the absorption line feature. The high output power of several mW yields a stronger signal and increases your

Fast and wide wavelength tuning is required for in situ systems. Most customers use a scan rate of 10 kHz and benefit from our very large tuning coefficient.

measurement precision.

"Do not change your ideas, let us deliver a laser that fits your application."

We offer various packaging options, e.g. several free space housings including TEC and NTC, fiber coupling, collimation and custom designs. What do you require?

If you require custom specifications, please contact us. Nearly 80 % of our devices are more or less customer-specific. As nanoplus is a fully vertically integrated company, we control the entire process chain from design to packaging. Both nanoplus production facilities are based in Germany. To guarantee consistent product quality we apply a strict and ISO certified quality management system at all levels.

Our sales and R&D teams have long-standing experience in developing lasers. They will advise you in your design and realization phase as well as after-sales: We make market leaders!

TO5. TO56 and fiber coupled butterfly package

Schematic DFB with spectrum λ

Any custom wavelength is possible: You tell us what you need and we deliver it. With our patented DFB technology we design any wavelength between 760 nm and 14 µm.

Our excellent spectral purity is characterized by a large side mode suppression ratio (SMSR) of > 35 dB, giving your system a low signal to noise ratio against crossinterference.

ERED COL ISC 9001 4001











Typical Specifications: 1300 nm - 1650 nm

This data sheet reports performance data of a **sample nanoplus DFB laser at 1512 nm**, which is representative for the entire wavelength range. We offer enhanced specifications for 1392.0 nm, 1512.2 nm, 1560 nm, 1570 nm, 1580 nm and 1590 nm. Please refer to our <u>TOP Wavelengths</u> for further details: <u>https://nanoplus-usa.com/products/dfb-laser/</u>.



Typical room temperature cw spectrum of a nanoplus DFB laser at 1512 nm



Typical mode hop free tuning of a nanoplus DFB laser at 1512 nm by current and temperature

electro-optical characteristics	symbol	unit	min.	typ	max.
operating wavelength (at $T_{_{\mathrm{op}}},I_{_{\mathrm{op}}})$	$\lambda_{_{op}}$	nm		Please specify to 0.1 nm.	
optical output power (at $\boldsymbol{\lambda}_{_{op}})$	P _{op}	mW		5	
operating current	I _{op}	mA		70	
operating voltage	$V_{_{op}}$	V		2	
threshold current	I _{th}	mA	10	30	55
side mode suppression ratio	SMSR	dB		> 35	
current tuning coefficient	C,	nm / mA	0.01	0.02	0.03
temperature tuning coefficient	C _T	nm / K	0.07	0.10	0.14
operating chip temperature	T _{op}	°C	+20	+25	+50
operating case temperature*	T _c	°C	-20	+25	+50
storage temperature*	Τ _s	°C	-40	+20	+80

laser packaging options

TO5 with TEC and NTC, black cap, AR coated window

TO56 without TEC or NTC, sealed, window

c-mount without TEC or NTC

butterfly package with TEC and NTC, SM or PM fiber, FC/APC connector

chip on carrier without TEC, with NTC

Technical drawings & accessories are available at: https://www.nanoplus-usa.com/products/packaging

Please contact <u>victor.perez@nanoplus.com</u> for customized specifications, quotes and further questions. Visit the <u>nanoplus website</u> for technical notes, application samples or literature referrals.

nanoplus America Inc., nanoplus-usa.com, phone: +1-720-453-2454, email: victor.perez@nanoplus.com [©]copyright nanoplus America Inc. 2023, all rights reserved. Technical data is subject to change without notice. * non-condensing