

Schematic DFB

with spectrum

λ

TOP WAVELENGTH

760.8 nm
1278.8 nm
1392.0 nm
1512.2 nm
1560 - 1590 nm
1651 & 1654 nm
1742.0 nm
1854 & 1877 nm

- 1854 & 187
- 2004.0 nm
- 2330 & 2334 nm
- 3240 & 3270 nm
- 3345 nm HP
- 3345 & 3375 nm
- 4524 & 4534 nm
- = 4565 nm HP

5184 & 5263 nm



TOP Wavelengths DFB: High-Power 4565 nm

nanoplus Distributed Feedback Lasers (**DFB**) are specifically designed for high-precision gas detection using tunable diode laser absorption spectroscopy (**TDLAS**). Our devices operate **reliably** in more than 50,000 installations worldwide. For more than 25 years nanoplus has set the standard for DFB laser technology and is the only manufacturer routinely providing DFB lasers at **any wavelength**.

Key features:

- MONOMODE
- CONTINUOUS WAVE
- ROOM TEMPERATURE
- MODE HOP FREE TUNING



Overgrowth-free DFB device processing

A **narrow linewidth below 3 MHz** guarantees ultra-precise scanning of the absorption line feature. The **high output power** of **several mW** yields a stronger signal and increases your measurement precision.

Fast and wide wavelength tuning is required for in situ systems. Most customers use a scan rate of 10 kHz and benefit from our very large tuning coefficient.

"Do not change your ideas, let us deliver a laser that fits your application."

Any **custom wavelength** is possible: You tell us what you need and we deliver it. With our

Our excellent spectral purity is characterized

signal to noise ratio against crossinterference.

patented DFB technology we design any wavelength **between 760 nm and 14 µm.**


by a large side mode suppression ratio (SMSR) of > 35 dB, giving your system a low

We offer **various packaging options**, e.g. several free space housings including TEC and NTC, fiber coupling, **collimation** and **custom designs**. What do you require?

If you require **custom specifications**, please contact us. Nearly 80 % of our devices are more or less customer-specific. As nanoplus is a **fully vertically integrated company**, we control the entire process chain from design to packaging. Both nanoplus production facilities are based in **Germany**. To guarantee consistent product quality we apply a strict and **ISO certified quality management system** at all levels.

Our sales and R&D teams have long-standing experience in developing lasers. They will advise you in your design and realization phase as well as after-sales: We make market leaders! TO66 with TEC and NTC, sealed with cap and AR coated window


Superior Specifications: High-Power 4565 nm





This data sheet reports performance data of a sample nanoplus High-Power DFB laser at 4565 nm with enhanced specifications.

Standard specifications are available at: http://nanoplus-usa.com/products/dfb-laser. These lasers are particularly suitable for nitrous oxide (N₂O) and carbon monoxide (CO) detection.



Typical room temperature cw spectrum of a nanoplus DFB laser at 4565 nm 4572 4568 4564 4564 4564 4564 4560 4556 4556 4552 80 100 120 140 current (mA)

> Typical mode hop free tuning of a nanoplus DFB laser at 4565 nm by current and temperature

electro-optical characteristics	symbol	unit	min.	typ	max.
operating wavelength (at $T_{_{op'}} I_{_{op}}$)	λ_{op}	nm		4565	
optical output power (at $\lambda_{_{op}}$)	P _{op}	mW		15	
operating current	I _{op}	mA			140
operating voltage	V _{op}	V		5	
threshold current	l _{th}	mA	20	30	40
side mode suppression ratio	SMSR	dB		> 35	
current tuning coefficient	C,	nm / mA		0.12	
temperature tuning coefficient	CT	nm / K		0.45	
operating chip temperature	T _{op}	°C	+15	+20	+40
operating case temperature*	T _c	°C	-20	+25	+55
storage temperature*	Τ _s	°C	-30	+20	+70

* non-condensing

laser packaging options

TO66 with TEC and NTC, black cap, AR coated window

Other packaging options may be discussed on request.

Technical drawings & accessories are available at: https://www.nanoplus-usa.com/products/packaging

Please contact <u>victor.perez@nanoplus.com</u> for customized specifications, quotes and further questions. Visit the <u>nanoplus website</u> for technical notes, application samples or literature referrals.

nanoplus America Inc., nanoplus-usa.com, phone: +1-720-453-2454, email: victor.perez@nanoplus.com ®copyright nanoplus America Inc. 2025, all rights reserved. Technical data is subject to change without notice.