DFB Quantum Cascade Lasers


(QCL): 6000 nm - 11000 nm




nanoplus Distributed Feedback Lasers (**DFB**) are specifically designed for high-precision gas detection using tunable diode laser absorption spectroscopy (**TDLAS**). Our devices operate **reliably** in more than 50,000 installations worldwide. For 25 years nanoplus has set the standard for DFB laser technology and is the only manufacturer routinely providing DFB lasers at **any wavelength**.

Key features:

- MONOMODE
- CONTINUOUS WAVE
- ROOM TEMPERATURE
- MODE HOP FREE TUNING





Overgrowth-free DFB device processing

Any **custom wavelength** is possible: You tell us what you need and we deliver it. With our patented DFB technology we design any wavelength **between 760 nm and 14 µm.**

Our excellent **spectral purity** is characterized by a large side mode suppression ratio **(SMSR)** of > **35 dB**, giving your system a low signal to noise ratio against crossinterference.

A **narrow linewidth below 3 MHz** guarantees ultra-precise scanning of the absorption line feature. The **high output power** of **several mW** yields a stronger signal and increases your measurement precision.

Fast and wide wavelength tuning is required for in situ systems. Most customers use a scan rate of 10 kHz and benefit from our very large tuning coefficient.

"Do not change your ideas, let us deliver a laser that fits your application."

We offer **various packaging options**, e.g. several free space housings including TEC and NTC, fiber coupling **collimation** and **custom designs**. What do you require?

If you require **custom specifications**, please contact us. Nearly 80 % of our devices are more or less customer-spec As nanoplus is a **fully vertically integrated company**, we control the entire process chain from design to packag Both nanoplus production facilities are based in **Germany**. To guarantee consistent product quality we apply a strict and **ISO certified quality management system** at all leve



High-Heatload (HHL) mount¹ incl. collimation

Our sales and R&D teams have long-standing experience in developing lasers. They will advise you in your design and realization phase as well as after-sales: **We make market leaders!**



ATTENTION

WAVELENGTH

760-830 nm

830-920 nm

920-1100 nm

1100-1300 nm

1300-1650 nm

1650-1850 nm


1850-2200 nm


2200-2600 nm

Typical Specifications: 6000 nm - 11000 nm



This data sheet reports performance data of a **sample DFB QCL at 7970 nm**, which is representative for the entire wavelength range.





Typical room temperature cw spectrum of a nanoplus DFB laser at 7970 nm

Typical mode hop free tuning of a nanoplus DFB laser at 7970 nm by current and temperature

electro-optical characteristics ¹	symbol	unit	min.	typ	max.
operating wavelength (at $T_{op'}$ I_{op})	$\boldsymbol{\lambda}_{\text{op}}$	nm		Please specify to 0.1 nm.	
optical output power (at λ_{op})	P _{op}	mW	10	20	
operating current	I _{op}	mA		500	1500
operating voltage	V _{op}	V		9	15
threshold current	I _{th}	mA		400	
side mode suppression ratio	SMSR	dB		> 35	
current tuning coefficient	C	nm / mA	0.05	0.1	0.15
temperature tuning coefficient	C _T	nm / K		0.7	
operating chip temperature	T_{op}	°C	-10	20	45
operating case temperature ²	T_{c}	°C	10	20	30
storage temperature ²	T_s	°C	0	20	50

¹ TM-polarized ² non-condensing

laser packaging options

High-Heatload Mount (HHL) incl. collimation

Other packaging options may be discussed on request.

Technical drawings & accessories are available at: https://www.nanoplus-usa.com/products/packaging

Please contact <u>victor.perez@nanoplus.com</u> for customized specifications, quotes and further questions. Visit the <u>nanoplus website</u> for technical notes, application samples or literature referrals.